

# Characteristics

## Lifetime

All Gamma Vacuum ion pumps are designed to operate for 45,000 – 50,000 hours at 1x10<sup>-6</sup> mbar. Lifetime increases linearly with decreased pressure. At 1x10<sup>-9</sup>, for example, an ion pump can last for many years.

## Vacuum Processing

Ion pumps are shipped under vacuum at pressures less than 1x10<sup>-10</sup> mbar. Certificates of conformance are provided and record all leak check points and pump characteristic values. RGA scans can be provided upon request.



Feedthroughs

Gamma Vacuum has standardized on the commercially available 10kV SHV feedthrough since 1996. For legacy purposes, alternate feedthroughs are available.



Heaters

Integrated heaters can be added to ion pumps for economical and efficient baking.

## Ultimate Pressure

Ion pumps are capable of reaching pressures below 1x10<sup>-10</sup> mbar. Ultimate pressure of an ion pump is dictated by overall system conditions and materials.

## Port Configurations

Each ion pump can be configured with a variety of pumping port options. Additional ports are available in most designs on the top, bottom, or side and can accommodate TSP or non-evaporable getter (NEG) modules.



Cables

In addition to incorporating the SAFECONN interlock system, high voltage cables are made of flexible silicone materials that are bakeable and have high radiation tolerance.

# Technical Data

Specifications					Compatibility			
	Speed (l/s)	Inlet Flange(S)	Dimensions mm (in.) (H x L x W, max)	Weight, kg (lbs)	SPC	QPC	MPC	TSP
<b>Small Ion Pumps</b>								
MINI	0.2	DN 16 (1.33 in.)	38 x 38 x 51 (1.5 x 1.5 x 2.0)	0.35 (0.8)	X			
3S	2 - 3	DN 16 (1.33 in.)	45 x 45 x 108 (1.8 x 1.8 x 4.3)	0.35 (0.8)	X			
10S	8 - 10	DN 35 (2.74 in.)	107 x 113 x 190 (4.2 x 4.4 x 7.5)	6 (13)	X			
25S	15 - 20	DN 35 (2.75 in.)	202 x 125 x 130 (8.0 x 4.9 x 5.1)	9 (20)	X	X		
45S	30 - 40	DN 35 (2.75 in.) DN 63 (4.5 in.)	209 x 251 x 130 (8.2 x 9.9 x 5.1)	16 (34)	X	X		
75S	40 - 75	DN 35 (2.75 in.) DN 63 (4.5 in.) DN 100 (6 in.)	277 x 242 x 130 (10.9 x 9.5 x 5.1)	19 (42)	X	X		
<b>Low Profile Ion Pumps</b>								
100L	80 - 100	DN 100 (6 in.)	325 x 325 x 128 (13 x 13 x 5)	29 (62)		X	X	
200L	160 - 200	DN 150 (8 in.)	325 x 413 x 233 (13 x 16 x 9)	49 (108)		X	X	X
300L	240 - 300	DN 150 (8 in.)	325 x 413 x 337 (13 x 16 x 13)	66 (145)		X	X	X
400L	320 - 400	DN 150 (8 in.)	325 x 413 x 413 (13 x 16 x 16)	72 (159)		X	X	X
400LX	320 - 400	DN 150 (8 in.)	508 x 413 x 233 (20 x 16 x 9)	115 (253)		X	X	X
600L	480 - 600	DN 150 (8 in.)	325 x 513 x 513 (13 x 20 x 20)	103 (226)		X	X	X
600LX	480 - 600	DN 150 (8 in.)	508 x 413 x 336 (20 x 16 x 13)	115 (253)		X	X	X
800LX	640 - 800	DN 150 (8 in.)	508 x 413 x 413 (20 x 16 x 16)	124 (273)		X	X	X
1200LX	960-1200	DN 150 (8 in.) DN 200 (10 in.)	537 x 513 x 513 (21 x 20 x 20)	206 (452)		X	X	X
<b>Tall Profile Ion Pumps</b>								
150TV	120 - 150	DN 100 (6")	338 x 247 x 231 (14 x 10 x 9)	32 (70)		X	X	X
300TV	240 - 300	DN 150 (6")	345 x 450 x 231 (14 x 18 x 9)	65 (143)		X	X	X
600TV	480 - 600	DN 150 (6")	525 x 450 x 305 (21 x 18 x 12)	109 (243)		X	X	X



Leybold GmbH  
 Bonner Str. 498 · D-50968 Köln  
 T +49 (0) 221-347-0  
 F +49 (0) 221-347-1250  
 info@leybold.com  
[www.leybold.com](http://www.leybold.com)

TiTan™ is a registered trademark of GAMMA VACUUM, USA  
 Manufactured by GAMMA VACUUM, USA



BICOM 13994.xx - 181.11.02 x.x.xx.xx  
 Printed in Germany on chlorine-free bleached paper  
 Technical alterations reserved

181.11.02



# TiTan™ Ion Pumps





# TiTan™ Ion Pumps

used in a wide variety of high and ultra-high vacuum environments


**Ion pumps are used in a wide variety of high and ultra-high vacuum (UHV) environments. They can reach the lowest possible vacuum for an economical cost. In addition, ion pumps have some technical advantages over other technologies:**

- Vibration Free Operation
- Low Maintenance
- Radiation Tolerance
- Low Operational Cost
- Pressure Indication
- Long Operational Life
- Bakeable
- Permanent Gas Capture
- Non-contaminating Technology

## Applications



**Industry and Medical Processes**



**Semiconductor**



**Instrumentation**




**High Energy Physics**

## Small Ion Pumps (MINI - 75S)



Small ion pumps come in a wide variety of sizes and configurations. Gamma Vacuum maintains stock of the most common configurations for same-day shipping. These pumps have the added advantage that they can be mounted in any orientation without additional support.

## Low Profile Ion Pumps (100L - 1200LX)



Low Profile ion pumps are under 12 in. (300 mm) high for standard configurations. Custom built to each order, the closed magnetic loop of these pumps reduces the stray magnetic field created by the pump making these pumps ideal for any type of charged particle application.

## Tall Profile Ion Pumps (150TV - 600TV)



Tall Profile ion pumps are designed for mounting in narrow locations and matching competitive dimensions. These pumps are built to order and designed to fit into locations where a Low Profile ion pump might not fit.

## TiTan™ Ion Pump Elements

TiTan™ ion pump elements are “tuned” for specific pumping applications. Surfaces are chemically processed to remove potential surface contaminants and provide maximum adhesion for extended lifetime. Ceramics are optimally shielded to reduce exposure to sputtered material.



- TiTan™ CV (Conventional) – two titanium cathodes for high pumping speed of reactive gases.
- TiTan™ DI (Differential) – a titanium and tantalum cathode for maintained pumping speeds of reactive gases and long term stability of noble gases.
- TiTan™ TR – classic triode element for higher pressure operation